

Simoloyer® CM08-AB08

High Kinetic Processing mode

batch operation, auto-batch, semi-continuous

in general

High Kinetic Processing (HKP) in the Simoloyer® represents the most advanced technique for Mechanical Alloying (MA), High Energy (HEM) and Reactive Milling (RM), for making Nanostructures. To cover requirements from lab to industry for quality and quantity, processing modes batch-, auto-batch and semi-continuous operation do provide the most advanced solutions. While the Simoloyer® base unit remains same, grinding units are equipped with corresponding mainports. Standard for batch operation, type -s2 with second mainport for auto-batch and type -s1 with semi-continuous ports for insitu separation/classification at carrier-gas/multiphase flow. All types cover batch operation, multiple mainports are available up to type -s5 and exceeding.

application

Automatic batch-processing, for battery materials cathode, anode, particularly Li/Ion. ODS/NFA, both, Fe- and Ni-base manufacturing. Solid-state hydrogen storage, hard-metal applications, composite materials, rapid particle size reduction of brittle solids vs. ductile metal flakes and multiple more.

advance

large-scale semi-automatic nanostructure processing with aerodynamic separation. Here Al-Flakes & propulsion in/with:

- closed system, controlled atmosphere & evacuation;
- modular setup, automatic valves for system and charging;
- carrier-gas discharging with automatic product separation;
- communication of all drives by Maltoz®-software/PLC;

➤ safe process, faster discharging for best product quality.

data & dimensions AB08

| | |
|---|--|
| AB08 (CM08 > 11kW) IP22 upon inquiry: 320-528V | 400VAC + PE, 3-phases (4 lines, TT/TN-net), 50/60Hz |
| power supply AB08 only | <5kW, 16A |
| dimensions (LxWxH) | 1820 x 950 x 3700mm |
| floor-plan / AB08 weight | 2 x 5m (10m²) / 290kg |

